



Dimensions

Dual-Threaded Electrodes

3-2839-1 (0.01 cell)




3-2840-1 (0.1 cell)




Dual threads 3/4 NPT
 or ISO 7/1-R 3/4 front
 and back

3-2841-1 (1.0 cell)*



Dual threads 3/4 NPT
 or ISO 7/1-R 3/4 front
 and back


3-2842-1 (10.0 cell)*



* Although these electrodes look similar in design, there is an inherent difference. From the bottom view, the 2841 electrode features a simple plastic insert. However, the 2842 electrode features a complex plastic insert with four holes through which liquid flows.

Integral Mount Sensor

The 2839-2842 Dual Threaded Conductivity Electrodes can be directly mounted to an integral version transmitter, using the 8052 Integral Mount Kit.



- X1 (3-2839-1) = 73 mm [2.88 in.]
- X2 (3-2840-1) = 35 mm [1.38 in.]
- X3 (3-2841-1) = 41.3 mm [1.63 in.]
- X4 (3-2842-1) = 41.3 mm [1.63 in.]